

23 Exhibition Drive, Malaga Western Australia

Monday - Friday 7am-5pm + Sat 8am-4pm

Sales Centre for Sales, Advice + Orders T +61 8 9209 7400 hello@beyondtools.com

LEATHER CARE BY GILLY'S





| SKU | Option | Part # | Price |
|---------|----------------------------|-----------|---------|
| 8729238 | Colour: Clear, Size: 100ml | LC100MLCL | \$20 |
| 8729240 | Colour: Clear, Size: 1L | LC1LCL | \$77 |
| 8729239 | Colour: Clear, Size: 200ml | LC200MLCL | \$29.95 |
| 8043269 | Colour: Clear, Size: 2L | LC2LCL | \$110 |

| Model | |
|-----------------------------|----------------|
| Туре | Leather Polish |
| SKU | 8729238 |
| Part Number | LC100MLCL |
| Barcode | 9324554000578 |
| Brand | Gilly's |
| Dimensions | |
| Product Weight (Net Weight) | 1 kg |
| Country of Origin | |
| Manufactured in | Australia |
| Packaging + Shipping | |
| Shipping Weight (Gross) | 0.28 kg |



Leather Care is a rich, nourishing, soft paste designed to penetrate dry leather and restore its suppleness. It contains beeswax and a citrus solvent, along with plant-based oil to create a water-repellent barrier. It is non-toxic and easy to use. Test on a small, inconspicuous area before full application to ensure you are happy with the finish.

Use For

All types of leather goods and furniture. Exception: not suitable for aniline or semi-aniline leather as the citrus solvent *may* disturb the finish.

Thanks to Mélanie from Live Dream Upcycle (footage) & aurusaudio.com (soundtrack)

Surface Ensure that the area to be treated is clean

Preparation and dry.

Apply sparingly with a clean, dry cloth in a

circular motion,

Wipe away any excess with another clean $% \left(1\right) =\left(1\right) \left(1\right)$

cloth.

Dry Time 20 minutes provided excess is wiped away.

Maintenance Depending on wear, if the surface becomes

dull or dry.

Clean Up Warm soapy water.

Options LC200MLCL

How to Apply



23 Exhibition Drive, Malaga Western Australia

Monday - Friday 7am-5pm + Sat 8am-4pm

Sales Centre for Sales, Advice + Orders T +61 8 9209 7400 hello@beyondtools.com

LC100MLCL LC2LCL LC1LCL